



Technical Data



- Max. 250mA/120V/9W AC/6W DC
- 2 pole
- momentary or alternate
- 8 contact functions
- temperature range:
 - low temp: -40/+75°C
 - high temp: -40/+160°C
- through-hole version





Dimensions





PCB layout





Dimensions (w/LED)





PCB layout (top view)






Dimensions (w/2 LEDs)









PCB layout (top view)



How to order

	1 5	+	1 6 2 7 0	+	1 6 3 0 0	+	1 6 3 2 4	
	Switch		Extender		Cap		Bezel	
	15501 mom. silver				00 blue	30 ultra blue		01 brown
	15551 alt. silver				01 brown	40 dusty blue		03 grey
	15502 mom. gold				02 green	42 aqua blue		06 white
	15552 alt. gold				03 grey	32 mint green		09 black
	15500 silent silver				04 yellow	33 tele grey		
	15401 mom. silver high temp.				05 golden	34 melon		
	15402 mom. gold high temp.				06 white	38 noble red		
	15420 silent gold high temp.				07 orange	50 metal dark blue		
	15451 alt. silver high temp.				08 red	53 metal light grey		
					09 black	57 metal dark grey		
						58 metal bordeaux		

	1 5	+	1 6 2 7 0	+	1 6 3 0 0	+	1 6 3 2 7	+	1 6 9 2 2
	Switch		Extender		Cap		16325		LED
									
							16326		
									
							Lens 16327		LED 16922
							02 green		02 green
							04 yellow		04 yellow
							08 red		08 red
							2 required		2 required

Ordering example: 15501 + 16270 + 1630008 + 1632509 + 1632708 + 1692208

For updates of products and/or changes of specifications please see www.mec.dk