





NOTES:


Insulator Material: PBT, UL 94V-0
 Contact Plating: Flash Gold
 Contact Material: Brass

Current Rating : 1A AC,DC
 Contact Resistance: 20mΩ Max.
 Dielectric Withstanding: AC 500V
 Insulator Resistance: 1000MΩ Min.
 Operating Temp.: -40°C~+105°C



| NUMBER OF POSITIONS | DIMENSIONS | | |
|---------------------|------------|-------|-------|
| | A | B | C |
| 06 | 26.92 | 5.08 | 22.86 |
| 08 | 29.46 | 7.62 | 25.40 |
| 10 | 32.00 | 10.16 | 27.94 |
| 12 | 34.54 | 12.70 | 30.48 |
| 14 | 37.08 | 15.24 | 33.02 |
| 16 | 39.62 | 17.78 | 35.56 |
| 20 | 44.70 | 22.86 | 40.64 |
| 24 | 49.78 | 27.94 | 45.72 |
| 26 | 52.32 | 30.48 | 48.26 |
| 30 | 57.40 | 35.56 | 53.34 |
| 34 | 62.48 | 40.64 | 58.42 |
| 40 | 70.10 | 48.26 | 66.04 |
| 50 | 82.80 | 60.96 | 78.74 |
| 60 | 95.50 | 73.66 | 91.44 |
| 64 | 100.58 | 78.74 | 96.52 |

| UNLESS TOLERANCE | |
|------------------|--------------|
| GENERAL | ANGLE |
| X ± 0.30 | X° ± 3.0° |
| .X ± 0.20 | .X° ± 2.0° |
| .XX ± 0.15 | .XX° ± 1.0° |
| .XXX ± 0.08 | .XXX° ± 0.5° |



| DRAW BY | | SCALE | SHEET | UNIT |
|------------|-----|-------|-------|------|
| DESIGN BY | 1:1 | 1/1 | MM | |
| CHECK BY | | | | |
| APPROVE BY | | | | |

CnC Tech,LLC

Part No.
3010-XX-003-13-00

| DRAW NO: | REV: |
|----------|------|
| | A |