



Combination ratcheting spanner OPEN RATCH, metric, double hex., offset

17



Art.No. 41171919
GTIN 4018754239245
Model 17 19 GEWINKELT

Label. Combination ratcheting spanner OPEN RATCH size 19mm L.252mm

- Description.**
- reversible
 - bi-hexagon
 - 72 teeth
 - for work in confined spaces, tight ratchet angle of only 5°
 - ring end offset by 15°
 - Chrome Alloy Steel, chrome plated

Advantages.

STAHlwILLE ratchet combination wrench 19 mm, interchangeable, ring end 15 ° angled with bi-hexagon, length 252 mm, chrome alloy steel, chrome-plated, 41171919

The integrated 72-sprocket ratchet provides a working angle of only 5° – facilitating efficient working even in confined spaces

Switchable ratchet for quick tightening and loosening of screws

High-quality, non-slip surface texture – for safe working even with oily hands



Technical Drawing.



Technical Attributes.

a1	8,7 mm
a2	11,5 mm
Number of teeth	72
Working angle	5 °
b	39,0 mm
d	34,0 mm
l	252 mm
Offset angle	15 °
Size [mm]	19 mm
Size 1 [mm]	19 mm
Size 2 [mm]	19 mm

Logistics data.

Length (packed, mm)	280
Width (packed, mm)	130
Höhe mm (verpackt)	25
Code	41171919
Weight (gross, kg)	1,225
Weight PAP (kg)	0,000
Weight PVC (kg)	0,012
GTIN	4018754239245
Numbers of content units per order units	5
Country of origin	OHNE
Region of origin	Ausländischer Ursprung
Customs tariff no.	82041100

GTIN-Code.



Images.



STAHLWILLE Eduard Wille GmbH & Co. KG

Lindenallee 27 · 42349 Wuppertal · Germany · Phone: +49 202 4791-0 · Fax: +49 202 4791-200
 info@stahlwille.de · www.stahlwille.de · Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal
 Copyright by STAHLWILLE Eduard Wille GmbH & Co. KG, Wuppertal