



RoHS Compliant



P/N	L
107-1024-BL-00050	500±30
107-1024-BL-00100	1000±30
107-1024-BL-00150	1500±30
107-1024-BL-00200	2000±40



Notes:
 1. Waterproof Rate: IP67
 2. Electrical Characteristics:
 Current Rating: 1A
 Voltage Rating: 30V

PIN OUT:

P1	_____
1	Red(24AWG)
2	White(28AWG)
3	Green(28AWG)
4	Black(24AWG)
Shell	_____
	Drain

ITEM	DESCRIPTION	MATERIAL	PLATING & COLOR	Q'TY
1	USB Plug	USB 2.0 SMD	N/A	1
2	Screw Nut	PC	Black	1
3	Gasket	EPDM	Black	1
4	Cable	UL2725 24AWG*2C+28AWG*1P+ADB OD:4.7 UV Resistant	Black(PVC Jacket)	A/R
5	Outer molding	TPU	Black	A/R
6	Inner molding	TPU	Natural	A/R
7	Heat Shrink Tube	OD:1.0 300V 125°	Black	1

CnC Tech
 Industrial Cable and Connector Technology

GENERAL TOLERANCE:
 X=±5
 .X=±0.5
 .XX=±0.3

	DRAWN:	
	CHECKED:	
	APPROVAL:	
B		
A	11-Jul-2019	FILE
REV	DATE	BY
DESCRIPTION: WATERPROOF USB PLUG CABLE ASSEMBLY		SIZE
PART NO: 107-1024-BL-00XXXX		A4