

## LED Work Light EL 4050 M, 49.98W, 4500lm, IP65, 1.5m H07RN-F3G1.0



### Technical data

Product number:	1171960503
EAN:	4007123675623
Luminous flux:	4,500 lm
Power consumption:	49.9 W
Luminous efficacy:	90 lm/W
Energy efficiency class:	F
Colour temperature:	6,500 K
Colour rendering index CRI:	81
Min.-Max. Nominal input voltage:	220V - 240V
Lifetime:	54,000 h



<b>Cable length:</b>	1.5 m
<b>Cable designation:</b>	H07RN-F 3G1,0
<b>Dimmable:</b>	No
<b>With socket outlet:</b>	No
<b>Impact strength:</b>	IK08
<b>Protection class:</b>	I
<b>Degree of protection (IP):</b>	IP65
<b>Colour:</b>	black, grey

## Product texts

For indoor and outdoor use, IP 65.

- \* Solid, modern aluminium housing.
- \* Space-saving due to foldable frame.
- \* Sturdy tubular steel frame with plastic protective corners and ergonomically shaped plastic carrying handle.
- \* Spotlight can be steplessly swivelled and locked.
- \* Suitable for mounting on brennenstuhl® tripods.

## Scope of supply

LED Work Light EL 4050 M