

brennenstuhl®

Rechargeable LED worklight SH 1000 MA, 1000lm, IP54



Technical data

Product number:	1173700005
EAN:	4007123681303
Luminous flux:	1,000 lm
Power consumption:	10 W
Colour temperature:	6,500 K
Nominal input voltage:	5 V
Battery capacity:	2.2 Ah
Battery voltage:	3.7 V
Light duration max.:	6 h
Battery charging time approx.:	3 h

Number of batteries:	1
Battery type:	Built-in battery pack
Battery technology:	Lithium-ion
Impact strength:	IK07
Protection class:	III
Degree of protection (IP):	IP54
Colour:	black, grey

Product texts

LED worklight ideal for a wide range of uses in the trades, at home, in the garden or for camping.

- * Design in compact and practical pocket format.
- * Multi-function holding system with carabiner ring and magnet for flexible positioning.
- * Lightweight and robust plastic housing.

- * With on/off switch and 3 different brightness levels (25%/50%/100%) and flash function.
- * Integrated Li-Ion battery 3.7 V/2.2 Ah with charge indicator.
- * Charging via micro USB charging cable (start-up is not possible during charging).

Scope of supply

Rechargeable LED worklight SH 1000 MA, 60cm Micro USB cable