

brennenstuhl®

Rechargeable LED Hand Lamp SANSA 400 A, 400lm



Technical data

Product number:	1177370
EAN:	4007123657711
Luminous flux:	400 lm
Total luminous flux secondary source:	70 lm
Power consumption:	3.3 W
Colour temperature:	6,000 K
Battery capacity:	2 Ah
Battery voltage:	3.7 V
Light duration max.:	80 h
Battery charging time approx.:	3 h



Number of batteries:	1
Battery type:	Built-in battery pack
Battery technology:	Lithium-ion
Fittings:	Other
Impact strength:	IK07
Protection class:	III
Degree of protection (IP):	IP20
Colour:	black, yellow

Product texts

Extremely slim lamp for tight spaces.

- * 12 super-bright SMD LEDs at front.
- * Additional switching step for 1 SMD LED in the lamp head.
- * Continuous dimming function 0 to 100 % for particularly long lighting duration.
- * Charging period approx. 3 hours.
- * Rubber-clad housing.
- * Bendable and rotatable lamp head, foldable to pocket format.
- * 2 magnets at the back, one in the holding foot and fold-out hook for flexible use.
- * Integrated Li-Ion battery 3.7 V/2.0 Ah with charging indicator.
- * USB charging interface, including USB charging cable.