




# Сопла для НСТ-900

Форма сопла	Артикул	Наименование	размер	A	B	C	D
	A1125	ST, QFP	10x10	10.2	10.2	10	10
	A1262	ST, QFP	12x12	12.2	12.2	12	12
	A1126	ST, QFP	14x14	15.2	15.2	15	15
	A1127	ST, QFP	17.5x17.5	19.2	19.2	19	19
	A1128	ST, QFP	14x20	15.2	21.2	15	21
	A1261	ST, QFP	20x20	20.2	20.2	21	21
	A1182	ST, BQFP	24x24	24.2	24.2	21	21
	A1129	ST, QFP	28x28	29.7	29.7	29	29
	A1263	ST, QFP	28x40	27.7	39.7	29	39
	A1265	ST, QFP	32x32	32.2	32.2	31	31
	A1264	ST, QFP	40x40	40.2	40.2	39	39
	A1135	ST, PLCC	17.5x17.5	18.5	18.5	15	15
	A1136	ST, PLCC	20x20	21	21	19	19
	A1137	ST, PLCC	25x25	26	26	24	24
	A1138	ST, PLCC	30x30	31	31	29	29
	A1139	ST, PLCC	12.5x7.3	9	14	6.9	6.9
	A1140	ST, PLCC	11.5x11.5	13	13	10	10
A1141	ST, PLCC	11.5x14	15	13	15	10	
	A1131	ST, SOP	4.4x10	4.8	10		
	A1132	ST, SOP	5.6x13	5.7	15		
	A1133	ST, SOP	7.5x15	7.2	16		
	A1132	ST, SOP	7.5x18	7.2	19		
	A1187	ST, TSOP	18.5x8	18.5	10		
	A1257	ST, SOP	11x21	11.7	21		
	A1258	ST, SOP	7.6x12.7	8.2	11.7		
	A1259	ST, SOP	13x28	13.5	29		
	A1260	ST, SOP	8.6x18	8.7	19		
		A1142	ST, Трубка изогнутая 1,5x3			1,5x3мм	
A1124		ST, Трубка 2,5			2,5мм		
A1130		ST, Трубка 4,4			4,4мм		
A2064		ST, Трубка 6,4			6,4мм		
A2084		ST, Трубка 8,4			8,4мм		
A2127		ST, Трубка 12,7			12,7мм		