



## 3L12 SERIES 1/2" DISC MANUAL RESET ROLLOUT LIMIT CONTROLS

Manual Reset Flame Rollout Limit Switches Designed for Safety in Gas Fired Furnaces, Unit Heater and Roof-Top Units

### FEATURES

- Loose ring, stainless steel mounting brackets.
- 1/4" quick connect terminations. 90° orientation to mounting holes.
- Manual reset.
- Stainless steel disc cup (A1 disc cup for 3L12-301).

### SPECIFICATIONS

Single pole, single throw  
Open on temperature rise  
Electrical Ratings

- Resistive . . . . . 15A @ 120 VAC, 10A @ 240 VAC
- Inductive . . . . . 3.0 FLA, 12.0 LRA @ 120 VAC; 1.5 FLA, 6.0LRA @ 240 VAC
- Pilot Duty . . . . . 125 VA

#### Dimensions

- 3L12-301 . . . . . Length (1.18"), case width (.81"), height (.83")
- Others . . . . . Length (1.70"), case width (.81"), height (.83")

Weight . . . . . 0.2 oz.

Agency . . . . . UL Recognized File #E19279  
CSA Certified File Number LR77886/LR109556  
VDE Lic. 118631

**NEW SERIES!**

Model Number	Fixed Temperature Settings		Switch	Therm-O-Disc	
	Cut-in	Cut-out	Action	Style	Type
3L12-130	Manual Reset	130	Open on Rise	36TX16	611863
3L12-135		135	Open on Rise	36TX16	611864
3L12-220		220	Open on Rise	36TX16	611865
3L12-230		230	Open on Rise	36TX16	611866
3L12-240		240	Open on Rise	36TX16	611867
3L12-250		250	Open on Rise	36TX16	611868
3L12-260		260	Open on Rise	36TX16	611869
3L12-300		300	Open on Rise	36TX16	611870
3L12-350		350	Open on Rise	36TX16	611871
3L12-301*		300	Open on Rise	36TX16	611971

\*Specifically designed for ICP part #1013102

