

## DCD805NT-XJ

### 18V XR Brushless Hammer Drill Driver - Bare unit

The DCD805 is our latest and most powerful brushless 2 speed Hammer Drill Driver that delivers up to 90Nm of torque in a compact 177mm body, engineered to give you the greatest performance on the toughest jobsites. 2 speed and 15 torque settings give you the ultimate control over your drilling and fastening applications. An enhanced pivoting LED positioned on the foot offers greater visibility in dark and confined spaces. Part of the 18V XR range of 250+ tools and batteries.

### Selling Propositions

- Brushless Motor Technology for excellent efficiency
- powerful 18V XR Brushless XRP Hammer Drill with Compact Design
- Ultra compatto e leggero per applicazioni in spazi ristretti e per il massimo comfort d'uso
- 3-Mode Foot LED light with Pivoting Feature for working better in low visibility area
- 15 position adjustable torque control for consistent screw driving into a variety of materials
- Ergonomic design with rubber grip over-mould improving user's comfort
- Intelligent trigger design allows for total control of application
- Two speed all metal transmission for increased runtime and longer tool life
- Steel belt hook and magnetic bit holder ensures strong storage solutions

### Standard Equipment

### Warranty specifications

- DEWALT 3 year European PT Guarantee (subject to registration)

Specifications	
Max. Drilling Capacity (Wood)	55.0 mm
Max. Drilling Capacity (Metal)	13.0 mm
Max. Drilling Capacity (Masonry)	13.0 mm
Max Torque (Hard)	90.0 Nm
No Load Speed (Drilling/ Driving Mode)	2000 rpm
Beats per Minute	34000 bpm
No Load Speed (Hammer Mode)	2000 rpm
Battery Voltage	18 V
Power Output	850.0 W
Chuck capacity	13 mm
No. of Speeds	2.0
Weight	1.34 kg