

Shape


KPEG813



Model Number	KPEG813
Rated Voltage (Vp-p)	Max. 30
Current Consumption (mA)	Max. 6@10Vp-p,Square Wave,4.0KHz
Sound Pressure Level (dB)	Min. 84dB@10cm / 10Vp-p,Square Wave,4.0KHz
Electrostatic Capacity (pF)	12,000±30%@1KHz / 1V
Operating Temperature (°C)	-30 ~ +85
Storage Temperature (°C)	-40 ~ +95
Weight (Gram)	2.5
Material	ABS UL-94 1/16" HB High Heat (Black)

Dimension

Dimension



Tol : ± 0.5 Unit : mm

Characteristic

A: Frequency Response, Magn dB re 20.00uPA

