


## Coaxial Cable Connector 25\_N-50-3-20/133\_N

### Description

Straight panel cable jack, flange mount

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz

#### Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0383 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00009929
Catalogue drawing	DCA-00009931
Assembly instruction	DOC-0000179851
Mounting hole	DOU-00008795

### Ordering Information

Single package	25_N-50-3-20/133_NE
----------------	---------------------

### Additional Information

Suitable cables	RG_400_/U, ENVIROFLEX_142, RADOX_RF_400, ASNE0293 XF
-----------------	--