




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORPORATION.

PANDUIT PART NUMBER	DIMENSIONS				MAXIMUM CABLE DIA. in. (mm)	ADHESIVE BACKING	WEIGHT lbs/100 pcs (g)/100 pcs
	A	B	C	D			
ACC62-A							
ACC62-AT	1.12 (28.5)	1.24 (31.4)	.73 (18.5)	0.65 (16.5) (REF)	0.62 (15.7)	RUBBER	0.96 (437)
ACC62-AV						ACRYLIC	
						HIGH BOND ACRYLIC	



NOTES:
 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

CAD FILENAME/LAYERS
 6035978D_DC_GB0239BB/00C

PANDUIT CORP.
 TINLEY PARK, ILLINOIS

ACC62-A, ACC62-AT, ACC62-AV
 ADHESIVE CORD CLIP

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
 (.XX) ±0.05 (1.31 (1.31) ±0.010 (0.25) (1.31) ±0.02 (1.51) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	DATE	MAT'L	DWG	SCALE
00C	11-6-09	TMSA	SMV	ADDED PART NUMBER ACC62-AV	GB0239BB	00C	KLN		9-11-92	NYLON 6/6	GB0239BB	FULL
00B	7/9/08	DJSM		REVISED AND RE-RELEASED TO TEAMCENTER REV HISTORY: TABULARIZED DIMS; REMOVED .86 AND .49 DIMS; REVISED DIM TO INCLUDE TAPE; .73 WAS .74; REMOVED TAPE, APPLICATION, AND WARRANTY NOTES	GB0239BB	00B			9-11-92	NYLON 6/6	GB0239BB	FULL
3	7/18/00	JAD		DIMENSIONS .63, .86, & .49 WERE CHANGED TO REF DIMENSIONS	GB0239BB	3			9-11-92	NYLON 6/6	GB0239BB	FULL