

Data sheet

Commercial Art.No.: 70.350.0635.0

Hood BAS GOT GG 6 M20 A0

revos BASIC size 6 hood with cable gland M20, lateral cable entry, single locking lever



| | |
|--------------------|---------------|
| Commercial Art.No. | 70.350.0635.0 |
| EAN | 4015573616813 |
| Order Unit | 1 |

Certificates / Approvals



Technical data

General

| | |
|--|---------------------|
| Housing material | Aluminium |
| Color | Grey |
| Surface | With powder coating |
| Degree of protection (IP) | IP54 |
| UV resistant | Yes |
| Inflammability class of insulation material acc. with UL94 | Other |
| Operating temperature range min. | -40 °C |
| Operating temperature range max. | 120 °C |

Model

| | |
|------------------------|----------------------|
| Construction | 6 |
| Model | male |
| Locking mechanism | Single locking lever |
| Cable entry | Sideways |
| Type of cable | Gland nut |
| With cable screw gland | Yes |
| Thread size M | 20 |
| Thread size PG | |
| Hinged lid | No |
| EMC-version | No |
| Length | 73.6 mm |
| Width | 43 mm |
| Height | 51 mm |

Classification

| | |
|------------|----------|
| ECLASS 8.1 | 27440202 |
| ETIM 7.0 | EC000437 |
| ETIM 6.0 | EC000437 |

| | |
|----------|----------|
| ETIM 5.0 | EC000437 |
| ETIM 4.0 | EC000437 |
| ETIM 3.0 | EC000437 |