


**non-return valve**  
**H-QS-10**  
 Part number: 153465



**Data sheet**

Feature	Value
Valve function	Non-return function
Pneumatic connection, port 1	QS-10
Pneumatic connection, port 2	QS-10
Mounting type	Line installation
Standard nominal flow rate	1,480 l/min
Operating pressure	-1 ... 10 bar
Ambient temperature	0 ... 60 °C
Material housing	Anodised aluminium
Housing colour	silver
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Product weight	63 g
Materials note	Free of copper and PTFE Conforms to RoHS