

# plastic tubing PUN-10X1,5-SI

Part number: 152588

★ Core product range

FESTO



## Data sheet

| Feature                                  | Value  |
|--|--|
| Outside diameter                         | 10 mm  |
| Bending radius relevant for flow rate    | 54 mm  |
| Inside diameter                          | 7 mm   |
| Min. bending radius                      | 28 mm  |
| Tubing characteristics                   | Suitable for energy chains in applications with high cycle rates |
| Tubing test conditions                   | Suitable for energy chains: > 5 million cycles to FN 942021      |
| Temperature dependent operating pressure | -0.95 ... 10 bar   |
| Operating medium                         | Compressed air in accordance with ISO8573-1:2010 [7:-:-]         |
| Material fire test                       | UL94 HB  |
| Ambient temperature                      | -35 ... 60 °C  |
| Authorisation                            | TÜV  |
| Product weight according to length       | 0.0489 kg/m  |
| Pneumatic connection                     | For push-in connector outside diameter 10 mm                     |
| Colour                                   | silver   |
| Shore hardness                           | D 52 +/-3  |
| Materials note                           | Free of copper and PTFE<br>Conforms to RoHS                      |
| Material tubing                          | TPE-U(PU)  |