










## 7455

## TORQUE WRENCHES WITH SCALE, METAL HANDLE



- Mechanical torque wrench
- Accuracy:  $\pm 4\%$  (tightening) and  $\pm 6\%$  (reverse)
- Fixed ratchet head
- 32 teeth/11.25° action
- Dual scale, metric and imperial
- ISO 6789

		 731415			 Nm	 lb.ft	 lb.in	 L mm	 g
7455-5	0119639	1	1/4	1-5	.74-3.7	8.9-44.3	258	386	
7455-15	0119646	1	3/8	3-15	2.2-11.1	26.5-132.8	258	409	
7455-20	0125074	1	3/8	4-20	3-14.8	35.4-177	258	386	
7455-25	0125081	1	3/8	5-25	3.7-18.4	44.3-221.3	286	431	
7455-60	0125098	1	3/8	10-60	7.4-44.3	88.5-531	406	1135	
7455-100	0125111	1	3/8	20-100	14.8-73.8	177-885	406	1135	
7455-200	0125128	1	1/2	40-200	29.5-147.5	354-1770	483	1430	
7455-300	0125104	1	1/2	60-300	44.3-221.3	531-2655	457	1453	
7455-340	0125135	1	1/2	60-340	44.3-221.3	531-3009	620	1430	
7455-500	0125142	1	3/4	100-500	73.8-368.8	885-4425	870	4676	
7455-800	0125159	1	3/4	150-800	110.6-590	1328-7081	1067	5380	
7455-1500	0125166	1	1"	300-1500	221.3-1106.4	2655-13275	1778	11395	
7455-2500	0125173	1	1"	500-2500	368.8-1844	4425-22125	2756	22133	