

- Quick Links
- Cross reference
- RoHS/LF P/N Search
- Industry Standards
- Alphabetical List
- Documentation
- 3D model search
- Customer drawing search
- Multi Selection Search
- Search by category

Start > Search=10127717-04LF\* > 10127717-04LF

**10127717-04LF**  
**10127717-04LF - Minitek® Pwr 3.0 : Minitek® Pwr 3.0 Plug Housing, Dual row, 4 positions Glow Wire Compatible**



- Customer drawing
- Product Environmental Compliance Report

ACTIVE

RoHS Compliant

**Distributor Stock**

[Print Datasheet](#)

**FCI Brings You More**

- [Contact our sales/technical support](#)
- [Sample request](#)

- Specifications**
- Download document

**General Dimensional Electrical Mechanical Physical Approvals / Certifications Other Features**

<b>General</b>	
Number of contacts	4
Series	10127717
<b>Dimensional</b>	
Pitch	3.0
<b>Electrical</b>	
Withstanding Voltage	1000 VAC
Current rating	Up to 5 Amps
Resistance (Contact)	20 milliohm max. final 10 milliohm max. initial
Resistance (Insulation)	1000MΩ min
Voltage rating	250V
<b>Mechanical</b>	
Durability (Mating cycles)	100 Cycles
Insertion force	4.5N max
Withdrawal Force	2N min before durability, 1.5N min after durability
Glow Wire Compatible	Yes
<b>Physical</b>	
Color (Housing)	Black
Material (Housing)	High Temperature Thermoplastic
Temperature (Range)	-40°C to +105°C
<b>Approvals / Certifications</b>	
Approvals / Certifications	UL Approved
UL File Number	ML E467317
<b>Other Features</b>	
Packaging (Type)	PE Bag

Disclaimer : The information above is for reference only. For more technical details, refer to product specification and application specification.