

Housing - H4X:D4FM:AC - 1415796

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYPORT B24 panel mounting base, with single locking latch, with plastic protective cover, with stainless steel front plate connections, 1x D-SUB 25 (female/male), 1x 120 V AC outlet

Your advantages

- good shielding in the event of electromagnetic interference



Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	350.000 g
Country of origin	United States

Technical data

Dimensions

Height	30.5 mm
Width	53 mm
Length	140.5 mm
Length of the assembly cutout	113 mm
Width of the assembly cutout	35 mm

Ambient conditions

Degree of protection of housing (IP)	IP66
	IP67
Ambient temperature (operation)	-40 °C ... 125 °C (Housing)

General

Size	B24
------	-----

Housing - H4X:D4FM:AC - 1415796

Technical data

General

Color	gray aluminum
Torque	1.5 Nm ... 2 Nm (Mounting screw)
Protective cover	yes
Housing material	Die-cast aluminum, salt water resistant
Housing surface material	uncoated
Material lock	Polyamide
Material, protective cover	PA

Mechanical characteristics

Type	B24
Contact insert design	with 1x D-SUB 25 Socket/Pin #4-40 UNC bolts
	with 1x 120 V AC outlet Terminal 6.35 mm. AC outlet requires slip-on sleeves: Order no. 3240539 or 3240536


Electrical characteristics

Rated current	15 A ()
---------------	---------


Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings



Dimensional drawing



Mounting cutout

Classifications

eCl@ss

eCl@ss 8.0	27440101
eCl@ss 9.0	27440101

Housing - H4X:D4FM:AC - 1415796

Classifications

ETIM

ETIM 5.0	EC002560
----------	----------

Accessories

Accessories

Connector

Connector - C-SCFFI 2,5/4,8X0,5 - 3240539



Slip-on sleeve, fully isolated, blue, 1.5 ... 2.5 mm², for plug 4.8 x 0.5 mm

Connector - C-SCFFI 1,5/4,8X0,5 - 3240536



Slip-on sleeve, fully isolated, red, 0.5 ... 1.5 mm², for plug 4.8 x 0.5 mm