

## Male headers

### SL 22 190 56 G

square 0.635 mm, standard

[add to](#)



Features    Technical Drawing    Variants    Accessories / related products

<b>no. of contacts</b>	56
<b>contact material</b>	CuSn alloy
<b>surface contact / contact sleeve</b>	Ni+0,2µm Au Ni+4...6µm Sn
<b>surface of contact</b>	gold-plated
<b>volume resistivity</b>	
<b>nominal current</b>	3 A
<b>nominal voltage</b>	250 V AC
<b>test voltage</b>	2000 V
<b>material isolation body</b>	
<b>temperature range</b>	-40 °C ... +163 °C (260 °C / 10 s)
<b>class of flammability</b>	UL 94 V-0
<b>insulation resistance</b>	>10 <sup>12</sup> Ω
<b>connection type</b>	soldering
<b>version</b>	standard
<b>reflow solderable</b>	yes