




31-T IP

Thin Jaw Adjustable Spanners with Serrated Pipe Jaws & Phosphate Finish 209 mm Industrial Pack



PRODUCT DETAILS

- One end with serrated shark jaws for pipe fittings, loosening rounded nuts and bolts, working with round objects, etc. - equally strong in both directions
- Extra-wide jaw opening with a shorter handle than standard for working in confined spaces
- 36% thinner jaws than standard spanners of the same size for easier access in tight spaces
- Head combines slim design for accessibility with strength for performance
- Laser scale in mm for pre-adjusting and accurate measurement
- Precision hardening and high-performance alloy steel for top strength
- Phosphate finish, precision hardened and anti-corrosion treated
- Left going screw
- Standards: ISO 6787, DIN 3117, ASME B107.8 and BS 6333
- IP: Industrial pack



Follow the Fish!



PRODUCT ATTRIBUTES

Product	A	A	B	C	D	E	
31-T IP	209 mm	8 in	32 mm	4,5 mm	12,8 mm	29 mm	270 g

