




7154 TC

Precision Carbide Diagonal Cutters with Tapered Head for Hard Materials













PRODUCT DETAILS

- Carbide Insert Cutters suitable for hard wire materials such as Nitinol, Stainless Steel, Platinum and Titanium
- High performance alloy steel material provides strength and reliability
- Precision lap joint with screw minimizes friction while maximizing cutting edge and tip alignment
- ESD Safe, comfortable synthetic handles with return spring for smooth operation
- Polished, natural finish provides protection against oxidation
- Cutting capacity hard wire from 0.1 mm to 0.2 mm / 0.004 in - 0.01 in



PRODUCT ATTRIBUTES

Product: **7154TC**

	Tapered		M		Flush
	0.1-0.9 mm		0.004-0.03 in		0.1-0.4 mm
	0.004-0.02 in		0.1-0.2 mm		0.004-0.01 in
A	112.5 mm	A	4.43 in	B	13 mm
B	0,51 in	C	12,5 mm	C	0.49 in
D	6 mm	D	0,24 inch	F	2 mm
F	0,08 in		50 g		