



800ESD

Slotted ESD Safe Precision Screwdrivers 1.5-3.0 mm



PRODUCT DETAILS

- For slotted head screws
- ESD Safe Precision screwdriver, safely dissipates electrostatic charges, protecting electronic components from damage
- Specially designed for precision work, for mechanical and electronic applications
- Two-component ergonomic handle with soft grip material for comfortable grip
- The handle rotating head allows the tip to be perfectly positioned for fast comfortable finger movement during turning. The easy-movement rotating cap ensures rapid rotation and precise control
- Marking on the handle for an easy identification of tip
- Black oxide tip guarantees high accuracy and precision fitting
- High-performance alloy steel blade, chrome plated, for high protection against corrosion and long life span
- Standards: ISO 2380 and DIN 5264
- Standard IEC 61340-5-1, the electrical surface resistance of the ESD material amounts to 106-109 Ohm



PRODUCT ATTRIBUTES

Product								
800-1.5-50ESD	0.25 mm	1.5 mm	50 mm	2 mm	14 mm	87 mm	137 mm	12 g
800-2-50ESD	0.4 mm	2.0 mm	50 mm	2 mm	14 mm	87 mm	137 mm	13 g
800-2.5-50ESD	0.4 mm	2.5 mm	50 mm	2.5 mm	14 mm	87 mm	137 mm	14 g
800-3-50ESD	0.5 mm	3.0 mm	50 mm	3 mm	14 mm	87 mm	137 mm	15 g