

## Connection cable (protective contact) for extension leads without cable

Item no.: 9065x0050 (1.5m) | 9065x0000 (3m) | 9065x0100 (5m) | 9065x0150 (10m)



Connection cable in black


Length: 1.5m | 3.0m | 5.0m | 10.0m

Cable type: H05VV-F 3G1.5mm<sup>2</sup>

Plug: CEE7/7 Protective contact angle plug with double protective contact system




Open end: 280mm stripped (1.5 and 3m) / 220mm stripped (5m and 10m),  
blue + brown wire shortened by 110 mm each,  
all wires with ferrules (uninsulated 7mm)

Easy, fast and secure connection for e.g. EHMANN extension leads without cable



## Connection cable (protective contact) for extension leads without cable

Technical data

<p><b>3.600 W</b> <b>Power</b></p>	<p><b>230 V ~ (+/- 10%) / 50 Hz</b> <b>Rated Voltage</b></p>	<p><b>16 A</b> <b>Rated Current</b></p>												
<p>Safety class: IP20 Mark of conformity: VDE and KEMA KEUR</p>		  												
<table> <tr> <td>Item no. 9065x0050</td> <td>EAN 4012096005964</td> <td>PU 10</td> </tr> <tr> <td>Item no. 9065x0000</td> <td>EAN 4012096906506</td> <td>PU 10</td> </tr> <tr> <td>Item no. 9065x0100</td> <td>EAN 4012096906513</td> <td>PU 10</td> </tr> <tr> <td>Item no. 9065x0150</td> <td>EAN 4012096005971</td> <td>PU 10</td> </tr> </table>		Item no. 9065x0050	EAN 4012096005964	PU 10	Item no. 9065x0000	EAN 4012096906506	PU 10	Item no. 9065x0100	EAN 4012096906513	PU 10	Item no. 9065x0150	EAN 4012096005971	PU 10	
Item no. 9065x0050	EAN 4012096005964	PU 10												
Item no. 9065x0000	EAN 4012096906506	PU 10												
Item no. 9065x0100	EAN 4012096906513	PU 10												
Item no. 9065x0150	EAN 4012096005971	PU 10												