


BU-1404940

(12 Position Male to Female Receptacle Shielded Cable Assembly, 16.4')





J1 Male

J1 Female



J1	Twist Pair	COLOR	J2
1	Twist Pair 1	WHITE	1
3		BROWN	3
6	Twist Pair	GREEN	6
4	2	YELLOW	4
5	Twist Pair	GRAY	5
8	3	PINK	8
7	Twist Pair	BLUE	7
10	4	RED	10
9	Twist Pair	ORANGE	9
2	5	LIGHT GREEN	2
11	Twist Pair 6	BLACK	11
12		VIOLET	12
SHELL		BRAID	SHELL

- Mueller's BU-1404940 is a shielded cable assembly that has a 12-position Male plug to 12-position female receptacle.
- Shell size for connector: M12 (A Coding)
- Cable Material: Polyurethane
 - Overall length = 16.4' (5m)
- Coupling Nut: Anodized Aluminum
- Rating:

• Voltage: 30V AC/DC

- Current: 1.5 Amps
- Standard: IEC 61076-2-101
- Waterproof: IP67/IP68
- Temperature: -40°C to 105°C
- RoHS 3 Compliant

Mueller Electric Company 2850 Gilchrist Rd. Bld 5A Akron, OH 44305

www.muellerelectric.com

Toll Free: 800.955.2629 Phone: 330.780.2525 Fax: 330.780.2524