

Gaskets

Metal, for threaded plugs DIN 908

SPECIFICATION

Type

- Type **A**: Flat gasket

Copper **CU**

Aluminium **AL**



INFORMATION

The gaskets listed in this standard sheet are only an extract of DIN 7603.

They are used in connection with threaded plugs DIN 908 (see page 1681).

ON REQUEST

- other sizes
- other materials
- other types



* Complete with type index of the Gaskets

CU **AL**
Copper Aluminium

DIN 7603

Description	d1	d1 +0.3	d2	d2 -0.2	s ±0.2	Suitable for DIN 908	⚖️
DIN 7603-*-8-11,5-A	8	8.2	11.5	11.4	1	M 8 x 1	1
DIN 7603-*-10-13,5-A	10	10.2	13.5	13.4	1	M 10 x 1	1
DIN 7603-*-12-16-A	12	12.2	16	15.9	1.5	M 12 x 1.5	1
DIN 7603-*-14-18-A	14	14.2	18	17.9	1.5	M 14 x 1.5	1
DIN 7603-*-16-20-A	16	16.2	20	19.9	1.5	M 16 x 1.5	1
DIN 7603-*-18-22-A	18	18.2	22	21.9	1.5	M 18 x 1.5	1
DIN 7603-*-20-24-A	20	20.2	24	23.9	1.5	M 20 x 1.5	1
DIN 7603-*-22-27-A	22	22.2	27	26.9	1.5	M 22 x 1.5	1
DIN 7603-*-24-29-A	24	24.3	29	28.9	2	M 24 x 1.5	1
DIN 7603-*-26-31-A	26	26.3	31	30.9	2	M 26 x 1.5	1
DIN 7603-*-27-32-A	27	27.3	32	31.9	2	M 27 x 2	1
DIN 7603-*-30-36-A	30	30.3	36	35.9	2	M 30 x 1.5	1
DIN 7603-*-33-39-A	33	33.3	39	38.9	2	M 33 x 2	2
DIN 7603-*-42-49-A	42	42.3	49	48.9	2	M 42 x 2	2
DIN 7603-*-48-55-A	48	48.3	55	54.9	2	M 48 x 2	3
DIN 7603-*-10-13,5-A	10	10.2	13.5	13.4	1	G 1/8	1
DIN 7603-*-14-18-A	14	14.2	18	17.9	1.5	G 1/4	1
DIN 7603-*-17-21-A	17	17.2	21	20.9	1.5	G 3/8	1
DIN 7603-*-21-26-A	21	21.2	26	25.9	1.5	G 1/2	1
DIN 7603-*-27-32-A	27	27.3	32	31.9	2	G 3/4	1
DIN 7603-*-33-39-A	33	33.3	39	38.9	2	G 1	2
DIN 7603-*-42-49-A	42	42.3	49	48.9	2	G 1 1/4	2
DIN 7603-*-48-55-A	48	48.3	55	54.9	2	G 1 1/2	3

Weight AL