

## Data sheet

243-304

## MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR TERMINAL BLOCK



## Technical data

Package size 1000 10\*100 pieces.

pole count	4
Voltage UL	125 V
Voltage CSA	150 V
Current UL	7 A
Cross section from [AWG]	22 AWG
Cross section to [AWG]	20 AWG
Diameter from	0.6 mm
Diameter to	0.8 mm
Measured voltage EN	100 V
Measured shock voltage	1.5 kV
Pollution degree	2
Current intensity EN	6 A
Weight	0.76 g
Color	light grey
Wiring type	Side-entry
No. of connection Points	4
No. of potentials	1
Height	6.8 mm
Height	0.268 in
Width	10 mm
Width	0.394 in
Depth	10 mm
Depth	0.394 in

---

**Data sheet****243-304****MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR  
TERMINAL BLOCK**

---

Strip length from	5 mm
Strip length to	6 mm
Strip length	0.22 in

---

**Data sheet****243-304****MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR  
TERMINAL BLOCK**

---

<b>Approval</b>	<b>Voltage</b>	<b>Current</b>	<b>Approval number</b>	<b>Notes</b>
CCA	100	6	DK97-01026	
CSA	150		18677-31	
CSM	100	6	017956	
DEMKO	100	6	105047	
KEMA	100	6	92.6146.01	
NEMKO	100	6	L87233	
RMR	100	6	99.00007.250	
RosTesT	100	6	B09523	
SEMKO	100	6	9144043	
UL	125	7	E45172	
VDE	100	6	2574-1440-4031	

---

**Data sheet**

243-304

**MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR  
TERMINAL BLOCK**

---

**Accessories**

**Item number**

FIXING CARRIER FOR 4 PUSH-WIRE CONNECTORS

243-112

FIXING CARRIER FOR 6 PUSH-WIRE CONNECTORS

243-113