





SYM	ECN No.	MODIFICATION	DATE	ISSUED



Note:

1.Material:

1.1,Housing: High temperature

thermoplastic with/black g.f,UL94v-0

1.2,Contact: copper alloy,t=0.25mm

1.3,Shell: copper/Ferroalloy alloy,t=0.35mm

2.Specification:

2.1,Current rating:3A Max.

2.2,Dielectric withstanding

voltage: 100 V(ac) for 1 min.

2.3,Contact resistance: 30 mΩ Max.

2.4,Insulation resistance: 100 MΩ Min.

2.5,Total mating force: 3.57 Kgf Max.

2.6,Total unmating force: 1.0 Kgf Min.

3.Finish:

3.1,Contact: Plated Golt in Mating Area:

Tin On Solder Talls

Shell: Nickel Plating

4.Environmental:

4.1,Temperature range: -55°C~85°C

DRAWN		JTJ 深圳市精拓金电子有限公司					
CHECKED		TITLE		PART NO.			
APPROVED		AM大电流一体式（大縫隙） PBT红色/5A		917-111A110DAM0400			
				DRAWING NO. --			
	UNIT	TOLERANCE		SCALE	SHEET	SIZE	REV.
	mm	.XXX±.10, .XX±.15, .X±.25, ANG±1°		1:1	1 OF 1	A4	X1