

R 15-7+E-ISK-BU



Part number	09 15 007 3121
Specification	R 15-7+E-ISK-BU
HARTING eCatalogue	https://b2b.harting.com/09150073121

Identification

Category	Inserts
Series	R15

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	7
Details	for metal hoods / housings

Technical characteristics

Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	$>10^{10} \Omega$
Limiting temperature	-40 ... +125 °C
Mating cycles	≥ 500

Material properties

Material (insert)	Polyamide
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	HB



Pushing Performance

Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
----------	--

Commercial data

Packaging size	10
Net weight	8.85 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440223 Contact insert for circular connectors