

## Data sheet

243-144

## MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR TERMINAL BLOCK



## Technical data

Package size 1000 10\*100 pieces.

pole count	4
Cross section from [AWG]	20 AWG
Cross section to [AWG]	24 AWG
Diameter from	0.4 mm
Diameter to	0.5 mm
Measured voltage EN	100 V
Measured shock voltage	1.5 kV
Pollution degree	2
Current intensity EN	6 A
Weight	0.81 g
Color	transparent
Wiring type	Side-entry
No. of connection Points	4
No. of potentials	1
Height	6.8 mm
Height	0.268 in
Width	10 mm
Width	0.394 in
Depth	10 mm
Depth	0.394 in
Strip length from	5 mm
Strip length to	6 mm
Strip length	0.22 in

---

**Data sheet**

**243-144**

**MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR  
TERMINAL BLOCK**

---

Strip length

0.22 in

---

Data sheet

243-144

**MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR  
TERMINAL BLOCK**

---

Approval	Voltage	Current	Approval number	Notes
CCA	100	6	DK97-01026	
CSM	100	6	017956	
RMR	100	6	99.00007.250	
RosTest	100	6	B09523	

---

**Data sheet**

243-144

**MICRO PUSH-WIRE CONNECTOR FOR JUNCTION BOXES 4-CONDUCTOR  
TERMINAL BLOCK**

---

**Accessories**

**Item number**

FIXING CARRIER FOR 4 PUSH-WIRE CONNECTORS

243-112

FIXING CARRIER FOR 6 PUSH-WIRE CONNECTORS

243-113