


Number of contacts

max. 64



Female connectors

DIN Signal up to 2 A

Identification	Number of contacts	Part No.	Drawing	Dimensions in mm
Female connector for crimp contacts Order contacts separately	64	09 02 064 3214 ¹⁾	<p>View from termination side</p>	Shell housing 09 02 064 0501 / 09 02 064 0502 see chapter 20

Identification	Part No.	Performance levels according to IEC 60603-2. Explanation chapter 00
	2	1


Identification	Part No.	Performance levels according to IEC 60603-2. Explanation chapter 00
Female crimp contacts BC		
Bandoliered contacts (approx. 5,000 pieces)	09 02 000 6484	09 02 000 6474
Bandoliered contacts (approx. 500 pieces)	09 02 000 8434	09 02 000 8444
Individual contacts ¹⁾	09 02 000 8484	09 02 000 8474

Wire gauge mm² AWG Insulation ø mm
 0.09 - 0.5 28 - 20 0.7 - 1.5

3.5 + 0.5 mm of insulation is stripped from the wires to be crimped

For the fabrication in line with the specification please use exclusively crimp tools approved by HARTING (see DIN EN 60352-2)

Insertion, removal and crimping tools see chapter 30



Bandoliered contacts

Individual contacts

¹⁾ Packaging unit 1,000 pieces
²⁾ Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2