

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0386608804](#)
Status: **Active**
Overview: Beau Barrier Strips
Description: 12.70mm Pitch Beau PCB Tri-Barrier Terminal Strip, without Mounting Ends, 600V, 4 Circuits

Documents:

[3D Model](#) [3D Model \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Terminal Blocks
 Series [38660](#)
 Application N/A
 Component Type One Piece
 Overview [Beau Barrier Strips](#)
 Product Name Fixed Mount Barrier
 Type Barrier Strip
 UPC 883906403065

Physical

Circuits (Loaded) 4
 Circuits (maximum) 4
 Color - Resin Black
 Entry Angle Horizontal
 Lock to Mating Part None
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Polysulfone
 Net Weight 36.000/g
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 4.06mm
 PCB Retention Yes
 Panel Mount No
 Pitch - Mating Interface 12.70mm
 Pitch - Termination Interface 12.70mm
 Polarized to Mating Part N/A
 Shrouded Tri-Barrier
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -40° to +110°C
 Wire Size AWG 10, 12, 14, 16, 18, 8
 Wire Size mm² 0.75-6.00

Electrical


Current - Maximum per Contact 45.0A
 Voltage - Maximum 600V

Material Info

Engineering Number 66504-RC

Reference - Drawing Numbers

Sales Drawing SD-38660-003-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)4578-DC (25
 June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[38660 Series](#)

This document was generated on 07/16/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION