

# 1.8V CMOS COMPATIBLE SMD CRYSTAL CLOCK OSCILLATOR



5.0 x 3.2 x 1.1 mm

ASFL3



## FEATURES:

- Tri-state function
- Suitable for high density SMT
- Available tight stability option, +/-20ppm
- Seam sealed package assures high reliability
- Suitable for RoHS reflow

## APPLICATIONS:

- CCD clock for VTR camera
- Equipment connected to PC or PC cards
- Thin equipment
- Wireless communication

## STANDARD SPECIFICATIONS:

PARAMETERS	
ABRACON P/N:	ASFL3 Series
Frequency:	0.5 MHz to 125 MHz
Operating temperature:	-10°C to +70°C (see option)
Storage temperature:	-55°C to +125°C
Overall Frequency Stability:	±100 ppm max. (see option)
Supply voltage (Vdd):	1.8 Vdc ± 10%
Supply Current (Idd):	See table below
Symmetry at 1/2 Vdd:	40/60% max. (see option)
Rise and Fall Times (Tr/Tf):	See table below
Output load:	15pF max.*
Output Voltage:	VOH = 0.9*Vdd min., VOL = 0.1 *Vdd max.
Tri-state Function:	"1" or open; Oscillation; VIH > 0.7*Vdd, "0": Output disabled (HI-Z); VIL < 0.3*Vdd
Start-up-time:	See table below
Aging (First year):	±3 ppm max. @25°C
Period Jitter:	See table below


Table:

\* 30pF max is available. Please contact ABRACON.

Frequency range (MHz)	Idd mA (Typ)	Idd mA (Max)	Tr/Tf ns (Typ)	Tr/Tf ns (max)	Start-up time ms (Typ)	Start-up time ms (Max)	Period Jitter RMS ps (Typ)	Period Jitter RMS ps (Max)
0.5~9.999	2	5	5	10	3	5	2	3
10.000~29.999	5	8	3	6	3	5	2	3
30.000~49.999	8	10	3	6	3	5	2	3
50.000~69.999	5	10	2	5	3	5	2	3
70.000~99.999	8	15	2	5	4	10	2	3
100.000~125.000	12	20	2	4	4	10	2	3

## OPTIONS AND PART IDENTIFICATION:

(Left blank if standard)



ABRACON IS  
ISO9001:2008  
CERTIFIED



Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale  
30332 Esperanza, Rancho Santa Margarita, California 92688  
tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)

Revised: 09.05.12

# 1.8V CMOS COMPATIBLE SMD CRYSTAL CLOCK OSCILLATOR




5.0 x 3.2 x 1.1 mm


ASFL3




## OUTLINE DRAWING:



## TAPE & REEL: Tape and reel 1,000pcs/reel



## REFLOW PROFILE:



Need a test socket for the ASFL3 Series? To view compatible **PRECISION TEST & BURN-IN SOCKETS** for these parts, [click here](#).

**ATTENTION** Abracon Corporation's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependant Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon Corporation is required. Please contact Abracon Corporation for more information.

ABRACON IS  
ISO9001:2008  
CERTIFIED



Visit [www.abracon.com](http://www.abracon.com) for Terms & Conditions of Sale  
30332 Esperanza, Rancho Santa Margarita, California 92688  
tel 949-546-8000 | fax 949-546-8001 | [www.abracon.com](http://www.abracon.com)

Revised: 09.04.12