



DATASHEET

RIGID TOGGLE LATCH 40006 ZI

DESCRIPTION:

Stainless steel material or steel options

M4 fixing for catch and latch

Approximate fixing position to give approximate 25daN tension using catch plate: 45,5 mm

Maximum operating tension: 50daN

Hand operated and easy to use

Draw latch with over center fastener

Supplied with dimensions template for marking out and catch.

FEATURES:

- Finish: Zinc Plated
- Material: Steel
- Dimensions: 50 x 22.4 x 12 mm
- Depth: 12 mm
- Length: 50 mm
- Width: 22.4 mm

