



DATASHEET

FLEXIBLE TOGGLE LATCH 40019 ZI

DESCRIPTION:

Miniature, fully enclosed latch with a spring mechanism which gives a wide positioning tolerance.

Concealed catch plate with assembly rivets.

Compression springs made in Stainless Steel 18/8

Weld or M3 screw fixing

Maximum operating tension: 20daN

Latch to catch distance 25.5 mm

Supplied with dimensions template for marking out and catch.

FEATURES:

- Finish: Zinc Plated
- Material: Steel
- Dimensions: 34.5 x 18 x 8 mm
- Depth: 8 mm
- Length: 34.5 mm
- Width: 18 mm

