

ARCA 504021

Order symbol: ARCA 504021
Product nbr: 8120011
Description: Cabinet, PC
Remarks: Grey cover, 2-point locking, hinges on the long side

EAN: 6418074079220
EI. number:
 Finland: 3423099
 Denmark: 8212091090
 Sweden: 2500116
 Norway:



Sample photo

Including: Cabinet base, door with PUR gasket, mounting plate, screws for mounting plate. 3mm double bit lock(s) with key.
 S versions with swinghandle 3-point locking system. F versions with flange opening. Door guide included.

Dimensions:		Length	Width	Height	Rating:
mm:		500	400	210	Ingress Protection (EN 60529): IP 66
inch:		19.7	15.7	8.3	Impact Resistance (EN 62262): IK 10 +35°C /IK 08 -25°C
Materials:					
Material:		Polycarbonate			
Base colour:		RAL 7035			
Cover colour:		RAL 7035			
Gasket material:		PUR			
Temperatures:					
Short term:		-40 ... 120 °C			
Continuous:		-40 ... 80 °C			
Short term:		-40 ... 250 °F			
Continuous:		-40 ... 175 °F			
Accessories:					
MPS ARCA 5040		Mounting plate			
MPP ARCA 5040		Mounting plate perforated			
MPX ARCA 5040		Mounting plate			
DRS ARCA 504015		DIN rail frame set			
DRS ARCA 504021		DIN rail frame set			
IDS ARCA 5040		Inner door set			
PMK ARCA 40		Pole mounting kit			
		Certificates:			
		Fimko			

ARCA 500x400x210

ARCA 400x500x210

