

Rack PDU, Metered, 2U, 32A, 230V, (12) C13 & (4) C19

AP7822B



Call for More Information 0800 2799254

- Includes: Cord retention bracket(s), Installation guide, Rack mounting brackets, User manual

Output	
Nominal Output Voltage	230V
Overload Protection	Yes
Maximum Total Current Draw	32
Output Connections	(4) IEC 60320 C19 (12) IEC 60320 C13

Input	
Nominal Input Voltage	200V, 208V, 230V
Input frequency	50/60 Hz
Input Connections	IEC 60309 32 A 2P + E
Cord Length	3.7meters
Number of Power Cords	1
Load Capacity	7400VA
Maximum Input Current	32A

Physical	
Maximum Height	88MM, 8.8CM
Maximum Width	444MM, 44.4CM
Maximum Depth	112MM, 11.2CM
Rack Height	2U
Net Weight	3.36KG
Shipping weight	5.42KG

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

Technical Specifications

Physical	
Shipping Height	140MM, 14.0CM
Shipping Width	508MM, 50.8CM
Shipping Depth	368MM, 36.8CM

Environmental	
Operating Temperature	-5 - 45 °C
Operating Relative Humidity	5 - 95 %
Operating Elevation	0 - 3048meters
Storage Temperature	-25 - 65 °C
Storage Relative Humidity	5 - 95 %
Storage Elevation	0 - 15240meters

Conformance	
Approvals	C-Tick, CE, FCC part 15 class A, GOST, ICES-003, IRAM, MIC, VCCI, VDE
Standard warranty	2 years repair or replace

Sustainable Offer Status	
RoHS	Compliant

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.