



DATASHEET

FLEXIBLE TOGGLE LATCH 40022 ZI

DESCRIPTION:

Available with or without padlock facility.

Interchangeable with American models

Wide positioning tolerance created by spring mechanism

Failsafe design prevents over extension of links

Approximate mounting dimension with catch plate = 87 mm for a tension of approx. 35 daN

Maximum operating tension: 45 daN

Suitable for screw fixing using 2 x M5 screws for latch and 2 x M5 screws for catch

Supplied with dimensions template for marking out + catch plate

FEATURES:

- Finish: Zinc Plated
- Material: Steel
- Dimensions: 75 x 47,5 x 20,5 mm
- Length: 75 mm
- Width: 47,5 mm
- Depth: 20,5 mm

