

## Within Series Adaptor 37\_BNC-75-0-2/133\_N

### Description

Panel adaptor jack/jack, flange mount  
BNC jack (female) / BNC jack (female)

Interface standard  
Series BNC - Compatible with IEC 61169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance 75  $\Omega$   
Interface frequency max. 1 GHz

#### Mechanical Data

Number of matings 500  
Weight 0.0131 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Interface - BNC jack (female)

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

### Related Documents

Outline drawing DOU-00013603  
Mounting hole DOU-00009005

### Ordering Information

Single package 37\_BNC-75-0-2/133\_NE