

Han-Modular® 70 A Hybrid Module



Number of contacts

1 x 70 A

4 x 16 A



Identification	Part-Number		Drawings	Dimensions in mm
	Male insert (M)	Female insert (F)		
Han® 70 A Hybrid Module axial screw terminal				M
	6 ... 16 mm ²	09 14 005 2646		
				F
14 ... 22 mm ²	09 14 005 2647	09 14 005 2742		

Han Modular

Identification	Part-Number	Depiction
Hex Key SW 2.5 for axial screw terminal Bit ¼"	09 99 000 0375	

Identification	Wire gauge (mm ²)	Part-Number		Drawings	Dimensions in mm
		Male insert (M)	Female insert (F)		
Signal contacts crimp terminal silver plated	0.14-0.37	09 33 000 6127	09 33 000 6227		
	0.5	09 33 000 6121	09 33 000 6020		
	0.75	09 33 000 6114	09 33 000 6214		
	1	09 33 000 6105	09 33 000 6205		
	1.5	09 33 000 6104	09 33 000 6204		
	2.5	09 33 000 6102	09 33 000 6202		
	3	09 33 000 6106	09 33 000 6206		
	4	09 33 000 6107	09 33 000 6207		
gold plated	0.14-0.37	09 33 000 6117	09 33 000 6117		
	0.5	09 33 000 6122	09 33 000 6222		
	0.75	09 33 000 6115	09 33 000 6215		
	1	09 33 000 6118	09 33 000 6218		
	1.5	09 33 000 6116	09 33 000 6216		
	2.5	09 33 000 6123	09 33 000 6223		
	3	09 33 000 6106	09 33 000 6206		
	4	09 33 000 6119	09 33 000 6221		

Identification	Wire gauge		Stripping length
no groove	0.14 ... 0.37 mm ²	AWG 26-22	7.5 mm
no groove	0.5 mm ²	AWG 20	7.5 mm
1 grooves*	0.75 mm ²	AWG 18	7.5 mm
1 grooves	1 mm ²	AWG 18	7.5 mm
2 grooves	1.5 mm ²	AWG 16	7.5 mm
3 grooves	2.5 mm ²	AWG 14	7.5 mm
wide groove	3 mm ²	AWG 12	7.5 mm
no groove	4 mm ²	AWG 12	7.5 mm

*on the back crimp collar

Crimp contacts 0.14 ... 0.37 mm² only used with BUCHANAN crimping tool 09 99 000 0001

Stock items in bold type