

TGV103N

Weathersafe Vision Single Gang 13A Fused Spur

Features & Benefits

- Weathersafe Vision see through clear plastic cover
- Lockable cover facility
- Impact resistant housing
- Easy release lid catch
- Multiple M20 threaded screw outs
- Power ON neon indicator showing switch status
- Complies with BS1363
- IP66 weatherproof rating



Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface
Earth Class Rating	Class I
Operating Temperature	-5°C to 55°C
Ingress Protection Rating	IP66
Switch type	Double Pole Switch
Mounting Hole Centres (mm)	120 (Top/Bottom), 72 (Left/Right)
Cable Entry(s)	Back Entry, (Multiple M20 Threaded Screw-Outs Top/Bottom/Sides)

Data sheet

TGV103N

Safety / Weathersafe Vision Outdoor Power

General

Weight (g)	437
Height (mm)	148
Width (mm)	108
Depth (mm)	75.5
Body Construction	Polycarbonate (Impact Resistant)
Product Colour	Grey
Accessories (Included)	x2 Cable Glands
EAN Number	5012483012802
Guarantee Period	3 Years

Line Diagrams

