

CHERRY KC 1000



Models may vary from the image shown

Low Cost corded keyboard with whisper keystroke and abrasion-resistant labelling.

CHERRY KC 1000 is rock-solid CHERRY technology with an excellent price/performance ratio. Modern, flat design with gentle, quiet and durable wear-resistant keys. Universal, reliable and optimised for professional use. In black or grey.

Key benefits

- Flat, corded keyboard including cursor and number pad
- Whisper keystroke keys with wear-resistant laser key legends
- Up to 10 million keystrokes
- 4 hotkeys (calculator/e-mail, browser/sleep mode)
- Plug & Play via USB connection
- 3 blue status LEDs
- Optimised for professional use in the office (GS approval)

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

530 g

Total weight (with packaging):

768 g

Cable Length:

approx. 1.80 m

Storage Temperature:

-20°C to 65°C

Operating Temperature:

0°C to 50°C

Current Consumption:

max. 50 mA

Interface:

- USB

Product approvals:

- c-tick 
- UL 
- CE 
- FCC 
- TÜV/GS 

System requirements:

- USB connection

Delivery Volume:

- CHERRY KC 1000
- Operating instructions in hard copy

Dimensions (product):

458 x 170 x 17 mm

Packaging dimensions:

480 x 205 x 27 mm

Reliability:

- MTBF (90) > 80,000 hours

Keyboard:

- Key technology: LPK
- Service life, standard key: > 10 million key operations
- Number of Keys: Product dependant, see table "Models"
- Number of additional keys: 4

Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 30

Warranty:

2 years

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Housing colour	Key colour	Number of Keys
1	CHERRY KC 1000	JK-0800DE-0	4025112081309	Germany	light grey	light grey	104+4
2	CHERRY KC 1000	JK-0800DE-2	4025112081316	Germany	black	black	105+4
3	CHERRY KC 1000	JK-0800ES-2	4025112081347	Spain	black	black	105+4
4	CHERRY KC 1000	JK-0800EU-0	4025112081484	US English with EURO symbol	light grey	light grey	104+4
5	CHERRY KC 1000	JK-0800EU-2	4025112081491	US English with EURO symbol	black	black	104+4
6	CHERRY KC 1000	JK-0800FR-2	4025112081323	France	black	black	105+4
7	CHERRY KC 1000	JK-0800GB-2	4025112081330	UK	black	black	105+4