


Deep groove ball bearings, single row, shield on both sides



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
45	85	19	35,1	21,6	0,915	17000	8500	0,41	6209-2Z *



Calculation factors

k_r 0,025
 f_0 14