

Mid Office / Contact Centre Headset



TECHNICAL DATA

Microphone:

Directional:	Bi-directional
Impedance:	Max. 2.2K Ω 1KH(RL=2.2K Ω)
Sensitivity:	-43 $\pm$ 3dB RL=2.2K Ω Vs=2.0V (DC)
Frequency Range:	100-10000Hz
Operating Temp:	-25°C~+70°C
Storage Temp:	-40°C~+80°C

Speaker:

Impedance:	150 Ω $\pm$ 15% at 0.1 V1000Hz
Sound pressure:	129dB $\pm$ 3dB at 1000HZ
Frequency range:	FO ~20KHZ($\pm$ 10dB) FO: 210Hz $\pm$ 20%
Operating Temp:	-25°C 50°C
Storage Temp:	-25°C 60°C



PLX COMPATIBLE QD



CLOTHING CLIP



HEADSET BAG & HANGING HOOK



JPL-501S / 502S

Improved sound quality and a flexible microphone boom arm with **Surround Shield™** noise cancellation.

Overview

Features	Single or dual ear
	Left / right ear side compatible
	Clear, crisp sound
	Surround Shield™ noise cancelling microphone
	Sound Shield™ Acoustic Shock Protection
	'Put and stay' ratchet microphone boom arm
	Overhead, sure-fit fully adjustable headband
	Fitted with 55mm leatherette ear cushions for maximum all day comfort
What's included	Draw string headset storage bag, headset hanging hook, clothing clip and Quick Start Guide
Headset Weight	Mid-weight Headset, ~ 76g / ~110g
Connection	PLX fitted as standard or GN** compatible QD options
Compatibility	For full range of bottom leads* and compatibility information - Go to Jpltele.com
Certifications	CE, RoHS, REACH
Warranty	2 Years repair or replacement warranty
MOQ	Master Shipping Carton: 40
EAN:	JPL-501S-PM: 5060126956082, JPL-502S-PB: 5060126956105
SKU:	JPL-501S-PM: 575-264-001, JPL-502S-PB: 575-264-002

PLX = Plantronics compatible QD

* optional to purchase separately.

** GN QD available on special request

