

Specifications	Range	Best Accuracy		
		UT120A	UT120B	UT120C
Model		UT120A	UT120B	UT120C
DC Voltage (V)	400mV/4V/40V/600V	±(0.8%+1)	±(0.8%+1)	±(0.8%+1)
AC Voltage (V)	4V/40V/400V/600V	±(1.2%+3)	±(1.2%+3)	±(1.2%+3)
DC Current (A)	400μA/4mA/40mA/400mA			±(1.0%+3)
AC Current (A)	400μA/4mA/40mA/400mA			±(1.5%+5)
Resistance (Ω)	400Ω/4kΩ/40kΩ/400kΩ/4MΩ/40MΩ	±(1%+2)	±(1%+2)	±(1%+2)
Capacitance (F)	4nF/40nF/400nF/4μF/40μF/100μF		±(4%+3)	±(4%+3)
Frequency (Hz)	10Hz~10MHz	±(0.5%+3)	±(0.5%+3)	±(0.5%+3)
Features				
Display Count		4000	4000	4000
Auto Range		√	√	√
Duty Cycle	0.1%~99.9%	√	√	√
Diode		√	√	√
Auto Power Off	Around 30 minutes	√	√	√
Continuity Buzzer		√	√	√
Low Battery Indication	≤2.4V	√	√	√
Data Hold		√	√	√
Relative Mode		√	√	√
Input Impedance for DCV	Around 10MΩ	√	√	√
General Characteristics				
Power	3V Battery (CR2032)			
LCD Size	43mm X 22mm			
Product Color	Red and grey			
Product Net Weight	76g			
Product Size	110mm X 58.2mm X 10.8mm			
Standard Accessories	Battery, carrying case			
Standard Individual Packing	Blister, English manual			
Standard Quantity Per Carton	100pcs			
Standard Carton Measurement	750mm × 275mm × 490mm (0.1CBM per export carton)			
Standard Carton Gross Weight	21.9kg			