




3538 SINGLE BANJO BODIES

3538

3538 04 19 : brass body

maximum working pressure	bar 20	MPa 2,0	psi 290
working temperature	°C (Celsius) From -20 to 80	F (Fahrenheit) From -4 to 176	K (Kelvin) From 253 to 353
vacuum capability	mm Hg vacuum level of 755,000		
body	engineering grade polymer		
'O'-rings	nitrile		
gripping ring	stainless steel		



		ØD (mm)	C	ØG (mm)	H (mm)	L (mm)	L1 (mm)	L2 (mm)	(kg)
3538 03 19		3	M5x0,8	8,5	13,0	16,0	5,0		0,003
3538 04 10		4	G1/8	10,5	14,5	18,5	7,0		0,005
3538 04 19		4	M5x0,8	8,5	13,0	16,0	5,0		0,001
3538 06 10		6	G1/8	10,5	14,5	20,0	7,0		0,007
3538 06 13		6	G1/4	13,5	18,0	22,0	9,5		0,008
3538 06 19		6	M5x0,8	11,0	13,0	18,5	5,0		0,002
3538 08 10		8	G1/8	13,5	14,5	25,0	7,0		0,007
3538 08 13		8	G1/4	13,5	18,0	27,0	9,5		0,005
3538 08 17		8	G3/8	13,5	21,5	29,0	11,5		0,009
3538 10 13		10	G1/4	16,0	18,0	29,0	9,5		0,008
3538 10 17		10	G3/8	16,0	21,5	31,0	11,5	31,0	0,018
3538 10 21		10	G1/2	19,0	22,5	36,5	13,5		0,022
3538 12 17		12	G3/8	19,0	21,5	34,5	11,5		0,011
3538 12 21		12	G1/2	19,0	22,5	36,5	13,5		0,015