




The mechanical CL200 series are suitable for a wide range of light duty entry control applications. This premium range of light duty locks offers 5 functions in two PVD finishes. On request multiple locks can be supplied coded or keyed alike.

## Technical Specifications

<b>Functions:</b>	4 available
<b>Spindle Type:</b>	Flat spring loaded spindle
<b>Material:</b>	Zinc alloy
<b>Door thickness:</b>	200 5mm - 65mm (3/16" - 2 1/2")
<b>Door material:</b>	Suitable for wooden doors
<b>Buttons:</b>	14 stainless steel buttons
<b>Non handed:</b>	Locks will fit doors hung on the left or right
<b>Fitting:</b>	Easy fit
<b>Fitting Options:</b>	Vertical
<b>Finish:</b>	Stainless Steel and Polished Brass
<b>Codes:</b>	8, 191 non sequential codes available
<b>Code storage:</b>	Single code
<b>Key override:</b>	Available to order on any function. Keyed alike if required

### Key Override Option:




<b>Functions:</b>	
<b>Models:</b>	200, 210, 255, 290
<b>Mortice Latch:</b>	255 supplied with 'Hold open' function allowing free entry. Function can be disabled
<b>Mortice Deadbolt:</b>	210 bolt extends 25mm (1") beyond door edge when locked
<b>Surface Deadbolt:</b>	200 Stainless Steel finish only. Bolt is moved manually by outside knob after code input and freely by inside knob
<b>Back to back:</b>	290 mortice latch is supplied with two code plates to provide coded access in both directions
<b>Latch:</b>	Light duty with stainless steel latchbolt head, with "anit-shim" plunger, 60mm (23/8") backset requires 25mm (1") hole, 82mm (31/4") deep
<b>Also available to order:</b>	50mm (2") backset latch requires 25 x 72mm (1" x 27/8") hole 70mm (23/4") backset latch require 25 x 92mm (1" x 35/16") hole

## Code change method:

Requires removal of lock from door, simple code change following instructions provided

Use in offices / schools / warehouses / hospitals / care homes / nurseries / hotels / leisure facilities / the home.

### External Dimensions:



### Surface Deadbolt:

