

## 306A - CLICK WRENCHES WITH REMOVABLE RATCHET | R.306A25



### Description

- Factory accuracy:  $\pm 2\%$  except:
  - R.306-25D - K306-600D - K306-1000D ( $\pm 4\%$ ).
  - R.304DA ( $\pm 6\%$ ).
- Reliability of mechanism: 50 000 cycles (wrenches up to 200 N.m).
- Use possible with accessories:
  - End fitting: 9 x 12 or 14 x 18 mm.
  - Diameter: 30 mm.
- One-way wrenches usable for unscrewing by reversing the bits.
- Numbered wrenches supplied with ISO 6789 calibration certificate.
- Supplied in a plastic box with ratchet and hinged handle (except Ref R.306A25 - R.301A - K.306A600 - K.306A1000).

### Information

L [mm]	271
Attachment	9 x 12
Box	BP.D1
Capacity [N.m]	5 - 25
Wrench	R.306-25D
Ratchet	R.372
Contents	Box
Graduation [N.m]	0,10
Knob	-
[g]	450