



10
 JAHRE
 YEARS
 GARANTIE
 WARRANTY

ANSMANN FL7200AC

- ANSMANN Luminary BASE work floodlight with 80 W SMD LEDs and a lighting power of up to 7.200 lumens
- Extremely bright and homogeneously illuminated light for working in indoor and outdoor areas
- Integrated 500 cm long H07RN-F rubber cable for flexible use outdoors such as on construction sites, for moderate mechanical stresses.
- Splash-proof (IP65) - can be used indoors and out
- Robust aluminium and ABS housing – extremely shock-resistant
- Very pleasant LED light with a colour temperature of 5000K (daylight)
- Versatile use thanks to the sturdy adjustment bracket - the adjustable support can be adjusted up to 80°, and the light head a full 360°!
- The spotlight is very compact when folded up thanks to the adjustable bracket - the carry handle also enables it to be comfortably carried to the desired place of use

INFORMATION

Product name	FL7200AC
Part No.	1600-0404
EAN-Code	4013674172665
Customs tariff number	94054239000
Product content	FL7200AC, operating instructions

Product	360 × 353 × 91 mm / 3414 g
Packing + Product	360 × 91 × 353 mm / 3699 g
Packing Unit	4 (389 × 375 × 373 mm)

