

# Product Specification



<b>Input voltage</b>	AC 220V / AC 110V
<b>Power</b>	≤550W
<b>Heater type</b>	Skeleton
<b>Airflow type</b>	Diaphragm pump
<b>Airflow value</b>	≤24L / min
<b>Temperature range</b>	100°C - 450°C
<b>Temperature stability</b>	±1 °C
<b>Shows type</b>	LED / display
<b>Handle line</b>	≤100 cm
<b>Noise</b>	≤45dB
<b>Work Environment</b>	0 ~ 40°C
<b>Storage Environment</b>	-20 - 80°C
<b>Storage humidity</b>	35% - 45%